







I-HEXMRT™ Implant Drill Usage Chart

The drills for I-HEXMRT™ Implants utilize an improved design for increased efficiency, longevity and overall ease-of-use. To maintain optimal performance Keystone Dental recommends replacing drills after 20 uses (depending upon bone density). The chart below provides an easy method for tracking drill usage. Simply check the box next to the corresponding drill each time it is used. Then, order a replacement drill as you near 20 uses.

						CATALOG #
TWIST DRILLS						
	Ø2.0 mm Twist Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15829K
	Ø3.0 mm Twist Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15830K
TAPERED DRILLS						
	Ø2.0 mm Spade Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	G21243
						
	Ø3.5 x 8 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15840K
	Ø4.3 x 8 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15841K
	Ø5.0 x 8 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15842K
	Ø6.0 x 8 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15843K
						
	Ø7.0 x 7 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15831K
	Ø7.0 x 9 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15832K
	Ø7.0 x 11 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15833K
						
	Ø8.0 x 7 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15834K
	Ø8.0 x 9 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15835K
	Ø8.0 x 11 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15836K
						
Ø9.0 x 7 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15837K	
Ø9.0 x 9 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15838K	
Ø9.0 x 11 mm Tapered Drill	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	15839K	